

PRESS RELEASE Micromachine/MEMS 2009 from the 29th of July to the 31st of July 2009 in Tokyo/Japan booth E-17

Fraunhofer IPMS, Dresden carries out customer specific developments in fields of microelectronic and micro systems technology serving as a business partner that supports the transition of innovative ideas into new products. Fraunhofer IPMS develops and fabricates modern MEMS and OLED devices in its own clean room facilities. In addition to R&D services it offers ramp-up within a pilot production. With modern equipment and about 200 scientists and engineers, the range of projects and expertise covers sensor and actuator systems, microscanner, spatial light modulators, lifetronics as well as organic materials and systems.

At the Micromachine/MEMS 2009 in Tokyo Fraunhofer IPMS presents:

1. MEMS Spatial Light Modulator Demonstrator

MEMS Spatial Light Modulators (SLMs) are used to modulate the entire cross section of an incident beam of light simultaneously with high spatial resolution. Usually, MEMS thin film technology is used to fabricate an array of micromirrors on top of a CMOS backplane. Each mirror can be addressed and moved individually to control either intensity or phase of one pixel. SLMs are used in a range of applications from video projectors to Adaptive Optics (astronomy, ophthalmology) and mask writers in the semiconductor industry. Contrary to the digitally addressed SLMs in projectors that use time multiplexing to generate grey levels, the SLMs developed by Fraunhofer IPMS are addressed with analogue voltages that enable the chip to directly generate analogue intensities. Micronic Laser Systems ABs mask writers exploit this feature to shift the generated patterns with accuracies far smaller than the system's pixel resolution. The mirrors of the Fraunhofer IPMS device are specified for monochromatic light between 248 nm up to 520nm, enabling not only the use of the DUV excimer wavelengths, but also the less aggressive (and less costly) near UV light sources. One example where the mirrors could be used is pattern generation for printed circuit boards, but also other areas that require a combination of both, high resolution as well as throughput. The SLM is capable of addressing 1 million pixels at a framerate of 2 kHz (that is, 2 Gpixel/s). The demonstrator setup visualizes the function of the SLM. A green LED generates a light beam, lenses and mirrors guide the light onto the SLM, where it is modulated.

2. *Microscan* – a 1D scanner module

Based on its competence in developing and fabrication of micro scanner devices Fraunhofer IPMS presents a 1D micro scanner module. Its modular platform approach was developed to bridge the gap between the supply of bare micro scanner dies and the final integration in the customer application. With the drastic enhancement of the short term availability of OEM-capable customized solutions the institute proofs its competence for packaging, electronics development and system design. The application specific scanner system is based on a modular approach where several prefabricated components are chosen to meet our customers demands.

The complete modular platform consists of:

- A micro scanner device (selected from available devices or even customized fabricated at Fraunhofer IPMS),
- Chip carrier with hermetic housing (optional) and front optics,
- scanning mirror deflection control (optoelectronic sensor),
- Electronics for driving the micro scanner and the deflection sensor with a standard communication interface (SPI) and I/O ports.

A selected module based on the above-described platform is exhibited at Micromachine/MEMS 2009. This module comprises a 1D micro scanner device mounted on a ceramic substrate housed by a glass dome as optical interface,

an optical deflection sensor as well as the miniaturized driving electronics. A modular platform for 2D micro scanners is currently under development and will be available, soon.

3. MEMS Adaptive Optics

Adaptive Optics (AO) is mainly used for the compensation of spatially and timely varying wavefront disturbances within an optical system for an enhancement in optical imaging through inhomogeneous or turbulent media. Originally evolved from astronomy to compensate for atmospheric turbulences, AO techniques also can be used for aberration correction of the human eye in ophthalmology, for imaging through biological tissue in optical microscopy or for any kind of object recognition in machine vision. Furthermore, there are applications in laser beam shaping as well as in ultra-fast laser pulse modulation. The key component is formed by the actual wavefront controlling device. For that purpose MEMS (Micro-Electro-Mechanical-System) micro mirror arrays possess several attractive features. Due to their integrated fabrication capability they can support large pixel numbers providing an exceptional high spatial resolution for an improved reproduction especially of higher order phase aberrations. They also benefit from a step function display capability, fast mechanical response times, low power consumption, broad spectral bandwidth from IR down to DUV and polarization insensitivity. Compared to previous macroscale systems micro mirrors also offer the potential of a substantial cost decrease as well as a significant device miniaturization just facilitating completely new possibilities for a broader commercial exploitation. The Fraunhofer IPMS therefore has developed a complete MEMS Phase Former Kit. The key component is a high-resolution MEMS micro mirror array of 240 x 200 piston-type mirror elements with 40 µm pixel size providing 0.5 µm stroke at 8bit resolution corresponding to 1.0 µm phase shift in reflection. Full user programmability and control is established by a comfortable driver software for Windows XP® PCs supporting both a Graphical User Interface as well as an open ActiveX[®] programming interface for open-loop and closed-loop operation. High-speed data communication is accomplished by an IEEE1394a FireWire interface together with an electronic driving board allowing for maximum data transfer rates of up to 500 Hz. In order to visualize the potential for optical imaging enhancement a complete AO demonstrator system has been implemented. It basically comprises a projection system, where different image objects can be imaged through adaptive optics onto a CCD camera. Phase errors of different severness can be introduced by rotating phase plates. Using a Shack-Hartmann sensor and the Fraunhofer MEMS micro mirror for the detection and correction of the wavefront, the obtainable imaging improvement is visualized by means of the recorded CCD image displayed on a video screen. For a more guantitative performance characterization also MTF measurements have been carried out with the setup. Addressed business fields are optical system developer and manufacturer in the following areas:

- Machine Vision (in-situ process control through turbulent media)
- Optical Microscopy
- Ophthalmology
- Astronomy
- Laser Pulse Shaping
- Laser Beam Shaping
- Diffractive Optics (especially optical tweezers)

4. Lamda – Large aperture MEMS scanner module for 3D distance measurement

Traditional laser scanners for 3D distance measurement involve expensive, heavy and large rotating or vibrating mirrors as a means for light deflection of the scanning TOF (time of flight) distance measurement. Typically, the precision of TOF distance measurements is limited by the amount of signal light available at the detector. Hence, a scanning mirror with large aperture is required for LIDAR systems to collect small amounts of light reflected or scattered by the measured target. Its replacement by a micromechanical scanning mirror device is not straightforward, since a large mirror aperture of the receiver optics must by guaranteed in addition to sufficiently large optical scan angles (> 40°) and high scan frequency of more then 100 Hz. Contrary, the aperture of a single MEMS scanning mirror is limited to small values of typically 1...4 mm diameter due to the dynamic mirror deformation. The Fraunhofer IPMS has developed so far highly miniaturized MEMS scanner devices enabling significant large deflection amplitudes (up to 35°, mechanical) and low power consumption in electrostatic resonant operation, very promising for miniaturized and portable applications. Customized 1D/2D scanner devices are fabricated from single crystalline silicon in a qualified fully CMOS compatible MEMS process suitable for mass fabrication resulting in highly robust and reliable MEMS devices that withstand easily a shock of 2500 g.

Now the Fraunhofer IPMS presents at Micromachining/MEMS (Tokyo) for the first time the prototype of a new large aperture 1D MEMS scanner module especially designed for laser radar systems. The Lamda module is constructed based on a novel MEMS array of identical scanning mirror elements realized using the flexible MEMS technology of Fraunhofer IPMS. Therefore, Fraunhofer IPMS has designed a scalable MEMS scanner array composed of identical fb288.00] PM2009engl.doc

silicon mirror elements with a comparatively large total scanning aperture of 2.51 x 9.51 mm² and a large optical scan range of \pm 30°. The 1D MEMS scanner module comprises two separate scanning channels (a) a single scanning mirror of the collimated transmitted beam oscillates parallel to (b) a scanning mirror array of the receiver optics. Light paths of emitting and receiving optics are separated to reduce crosstalk in the final laser radar system. The receiver optics uses an array of 2 x 7 identical mirror elements resulting in a total aperture of 334 mm² and a filling factor of 80%. All mirrors are driven electrostatic resonant at 250 Hz by means of separate in-plane comb drives with identical frequency close to the mechanical resonance for oscillation around their long symmetry axes. Thus, the transmitted beam is sent via a separate emitting master mirror of the same mechanical dimensions as one element of the mirror array. Since laser energy is emitted in only one direction, all the receiving mirrors are synchronized to the master scanner by the driving control electronics to point in the same direction. Hence, the effective apertures of the receiving mirrors add up to form a sufficiently large aperture if all receiving mirrors are synchronized in phase to the emitting master mirror in order to maximize the optical signal of the detector system. To realize the mirror synchronization miniaturized position sensors are integrated into the Lamda module for each individual mirror element. Thus, a precise control of the mirror motion is achieved so that all receiving mirror elements can be slaved to the motion of the emission mirror. The Lamda scanner module has a total size of about 52 x 40 x 40 mm³ and provides a synchronous position signal of the actual scan angle required for the final 3D laser radar system. The MEMS array satisfies at the same time the demand of a comparatively large optically active area, 2.51 x 9.51 mm² per single mirror element, while keeping the resonance frequency of 250 Hz at a value that matches well to current TOF laser distance measurement systems the with point measurement rates of typical 250-1000 kHz. Thus, the optical scan range of ±30 degrees is split into 500 – 2000 intervals. The new concept of using an array of synchronized identical MEMS mirror elements for LIDAR systems permits large reception apertures while preserving the outstanding reliability, high scanning speed, compact size and small system weight that can be expected from MEMS. In comparison to systems with conventional scanner components, the new 1D MEMS scanner module enables 3D LIDAR systems to become significantly smaller and more robust. Higher scan rates can be realized without additional efforts (e.g. air bearings). Hence, the Lamda module is very promising for many applications e.g. in security, machine vision and even for portable outdoor use.

Further information are available:

Fraunhofer IPMS Ines Schedwill Marketing/Public Relations Maria-Reiche-Str. 2 01109 Dresden GERMANY Tel.: ++49 (0) 351/8823-238 Fax: ++49 (0) 351/8823-266 e-mail: Ines.Schedwill@ipms.fraunhofer.de Internet: www.ipms.fraunhofer.de